


POLYMEX

ION EXCHANGE RESIN



Description

Polymex Resin is a high capacity strongly acidic cation exchanger in bead form. It is based on cross-linked polystyrene and has a gel structure. The resin contains sulphonic acid functional groups. It is supplied moist in the sodium form.

Applications

Polymex Resin is used most widely in sodium form for water softening application. It can be used also in two-stage de-ionising as the cation exchanger in the hydrogen cycle.

POLYMEX

ION EXCHANGE RESIN

Polymex C-180

Features:

- High exchange capacity
- High mechanical strength
- Uniform particle with good hydraulics characteristic
- Good Selectivity
- Good Thermo-tolerant characteristic
- Excellent physical and chemical stability

Specification:

Polymer structure	: Styren-DVB
Functional group	: HSO ₃ ⁻
Appearance	: Light brown bead
Ionic form	: Na ⁺ type
Total exchange capacity	: ≥ 4.5 mmol/g(dry) (Na ⁺ type)
Total exchange capacity	: ≥ 1.9 mmol/ml (Na ⁺ type)
Moisture content	: 46-50% (Na ⁺ type)
Density	: 1.29 g/ml (Na ⁺ type)
Shipping weight	: 0.77.087 g/ml (Na ⁺ type)
Particle size	: 0.315-1.25 mm ≥ 95% <0.315mm ≤1%
Effective particle size	: 0.40-0.60mm
Uniformity coefficient	: ≤1.7
Attrition rate	: ≥90%
Swell, Max.	: Na ⁺ -H ⁺ 10%

Operation Parameters:

Operating temperature, Max.	: 120 °C
Bed depth, Min	: 800mm
Service flow rate	: 5-25BV ⁺ /h
Service flow rate	: 40 m/h
Regenerant	: NaCl HCl H ₂ SO ₄
Consumption (as 100%)	: 80-220g/l 50-150g/l 80-240g/l
Concentration	: 5-10% 5-8% 0.7-6%
Flow rate	: 2-8 BV ⁺ /h 2-5 BV ⁺ /h 2-20BV ⁺ /h
Contact time, Min	: 30 min
Slow rinse	: 2 BV ⁺ (Regeneration flow)
Fast rinse	: 4-8BV ⁺ (Service flow)

Note: 1 BV = 1 m³ media/1m³ resin



Packing

HDPE Lined bags 25 lts LDPE bags 1 cft/25lts

Storage

Ion exchange resins require proper care at all times. The resin must never be allowed to become dry. Regularly open the plastic bags and check the condition of the resin when in storage. If not moist, add enough clean demineralised water and keep it in completely moist condition. Always keep the resin drum in the shade. Recommended storage temperature is between 20 C and 40 C.

Safety

Acid and alkali solutions used for regeneration are corrosive and should be handled in a manner that will prevent eye and skin contact. If any oxidising agents are used, necessary safety precautions should be observed to avoid accidents and damage to the resin.

POLYMEX
ION EXCHANGE RESIN



Distribuidor



+ (591) 67408280 ✉ ventas@etrai.com

🌐 www.etrai.com

www.polymex.in

Ahmedabad • Mumbai • Delhi • Chennai • Kolkata • Hyderabad • Pune
Bangaluru • Tirupur • Visakhapatnam • Gauhati • Lucknow • Chandigarh • Jaipur